

# Model BD 23 | Standard-Incubators with natural convection

The BINDER incubator of the BD series with natural convection is the specialist in long-term and stable continuous operation. This incubator is specially designed for gentle incubation of organisms, as well as conditioning of heat-sensitive media or microbiological heating.

#### **BENEFITS**

- · Safe and reproducible incubation even under high batch throughputs in long-term operation
- Disinfection routine at 100 °C
- · Stable atmosphere by inner glass door



Model 23

#### **MAIN FEATURES**

- $\bullet~$  Temperature range: +5 °C above ambient temperature to +100 °C
- APT.line™ preheating chamber technology
- · natural convection
- · Adjustable exhaust air flap
- Controller with timer functions
- Inner door made of tempered safety glass

- 2 chrome-plated racks
- Stackable
- Class 3.1 independent temperature safety device (DIN 12880) with visual temperature alarm
- Computer interface: RS 422

#### **ORDERING INFORMATION**

Interior volume [L]	Voltage	Option model	Version	ArtNo.
20	230 V 1~ ph 50/60 Hz	Standard	BD023-230V	9010-0187
	120 V 1~ ph 60 Hz	Standard	BDo23UL-120V	9010-0189

#### **TECHNICAL DATA**

Description	BD023-230V1	BDo23UL-120V <sup>1</sup>
Article Number	9010-0187	9010-0189
Performance Data Temperature		
Temperature range +5 °C above ambient temperature to [°C]	100	100
Temperature variation at 37 °C [± K]	0.5	0.5
Temperature fluctuation at 37 °C [± K]	0.2	0.2
Heating-up time to 37 °C [min]	59	59
Recovery time after 30 seconds door open at 37 °C [min]	20	20


<sup>1</sup> All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



Description	BD023-230V1	BD023UL-120V1
Article Number	9010-0187	9010-0189
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50/60	60
Nominal power [kW]	0.2	0.2
Unit fuse [A]	12.5	12.5
Phase (Nominal voltage)	1~	1~
Measures		
Interior volume [L]	20	20
Net weight of the unit (empty) [kg]	27	27
Permitted load [kg]	25	25
Load per rack [kg]	12	12
Wall clearance back [mm]	160	160
Wall clearance sidewise [mm]	100	100
Internal Dimensions		
Width [mm]	222	222
Height [mm]	330	330
Depth [mm]	277	277
Doors		
Unit doors	1	1
Housing dimensions not incl. fittings and connections		
Width net [mm]	435	435
Height net [mm]	495	495
Depth net [mm]	520	520
Fixtures		
Number of shelves (std./max.)	2/4	2/4

<sup>1</sup> All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

# **DIMENSIONS** incl. fittings and connections [mm]





#### **OPTIONS**

Designation	Description	*	ArtNo.
	back		
	10 mm	01	8012-0390
	30 mm	01	8012-0397
	50 mm	01	8012-0399
	left		
	10 mm	01	8012-0388
	30 mm	01	8012-0047
	50 mm	01	8012-0051
Access port with silicone plug	right		
F.~5	10 mm	01	8012-0387
	30 mm	01	8012-0046
	50 mm	01	8012-0050
	top		
	10 mm	01	8012-0386
	30 mm	01	8012-0045
	50 mm	01	8012-0049
	100 mm	01	8012-0053
	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device		
Alarm function for overheating	120 V option model	01 01 01 01 01 01	8012-0470
overneuting	230 V option model	-	8012-0469
Analog output 4-20 mA	for temperature values (output not adjustable)	-	8012-0432
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-1110
	for temperature, measurement in center of chamber at specified temperature	-	8012-1129
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	_	8012-0921
temperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-0918
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-0915
Door lock	lockable door handle	=	8012-0318
Pt 100 temperature sensor	additional flexible Pt 100, interior, with external connection incl. LEMO connector (3-pin)	-	8012-0115
* Notes > See last page			

<sup>\*</sup> Notes > See last page

## **ACCESSORIES**

Designation	Description	*	ArtNo.
APT-COM™ 4 BASIC-	for simple logging and documentation requirements with up to 5 networked units.		
Edition	version 4, BASIC edition	-	9053-0039
APT-COM™ 4 GLP- requirements of FDA Regulation 21 CFR 11.	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.		
Edition	requirements of FDA Regulation 21 CFR 11. version 4, GLP edition	-	9053-0042
APT-COM™ 4	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
PROFESSIONAL-Edition	version 4, PROFESSIONAL edition	-	9053-0040
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-0016

<sup>\*</sup> Notes > See last page



Designation	Description	*	ArtNo.
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO <sub>2</sub> , O <sub>2</sub> , pressure, depending on unit		
	Digital in PDF format	-	7057-0001
Qualification documents	Hard copy inside folder	-	7007-0001
	$IQ/OQ/PQ$ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder $IQ/OQ$ ; parameters: temperature, $CO_2$ , $O_2$ – or pressure, depending on unit		
	Digital in PDF format	-	7057-0005
	Hard copy inside folder	-	7007-0005
NI-	chrome plated	-	8012-2031
Rack	stainless steel	-	8012-2046
Rubber pads	set anti-slip feet	-	8012-2030
Shelf, perforated	Stainless steel	-	6004-0052
Table on castors	stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm	-	9051-0018

<sup>\*</sup> Notes > See last page

#### **SERVICES**

Designation	Description	*	ArtNo.
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
Maintenance services			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0710
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0910
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0200
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0810
Calibration services			
Colibration postificate town available	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	03, 04, 05	DL30-0101
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	03, 04, 05	DL30-0102
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0127
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0109
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	-	DL50-0010

<sup>\*</sup> Notes > See last page



#### **NOTES**

- o1 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- o3 Sensor calibration is performed in an accredited calibration laboratory.
- O4 Calibration is performed according to the BINDER factory standard.
- OS Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

## **BINDER GmbH**

Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com



BINDER Asia Pacific (Hong Kong) Ltd. Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com

BINDER Environmental Testing Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

www.binder-world.com

Representative Office for CIS Moscow, Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17

russia@binder-world.com www.binder-world.com

BINDER Inc.
Bohemia, NY, USA
TEL +1 631 224 4340
FAX +1 631 224 4354
usa@binder-world.com
www.binder-world.us