



Fast defrosting

Fast defrosting significantly reduces defrosting periods with minimal temperature variations.



Clean

Control screen made of plastic with smooth surface for promoting hygiene.



FROSTER LABO 530/730

PRO-ACTIVE





















■ PRO-ACTIVE- Control:

Permanent, proactive monitoring of the performance data and alerts in the case of deviations – so that you can take countermeasures in good time before a fault threatens your chilled goods; world's most accurate temperature control in refrigerated areas thanks to two standard PT-1000 sensors.

- **External housing** made from galvanised sheet steel (rustproof), with white, anti-scratch powder coating. Length of the plug cable: approx. 3 m.
- Equipped with castors.
- Interior made from smooth aluminium with colourless protective coating. Gibs (every 15mm) for flexible interior
- Interior consists of five plastic-coated shelves on overlays.
- Extra-thick 70 mm energy saving insulation, made from high-quality, compression-moulded and environmentally friendly material.
- Self-closing door with easy-to-replace plastic magnetic seal frame, lockable.
- Door hinge on the right-hand side (by default, see illustration), or the left-hand side, can be retrofitted.
- Forced-air cooling with cross-flow blower, switches off automatically when you open the door, ensures a uniform temperature and minimizes temperature deviations.

- Automatic fast defrosting thanks to time-limited and temperature-monitored reversal of the refrigerant circuit.
- Condensate evaporates in stainless steel heated dish beneath the refrigerator floor.
- Key switch protected control panel against tampering. Membrane keyboard with digital temperature display and minimum/maximum temperature memory.
- Power failure alarm (visual and audible alarm), the monitoring unit remains in operation for approx. 30 hours on battery power.
- Warning functions with visual and audible alarm signal in the case of temperature deviations or other malfunctions. Door open alarm after 60 seconds.
- Alarms can be forwarded using a potential-free contact (e.g., to a mobile phone with optional GSM-Module or to a control centre).
- Data documentation can be read via USB interface with KIRSCH Datanet software.
- Rapid freezing cycle ensures that the goods to be cooled are frozen quickly.
- Ventilation-enforced refrigerating machine, hermetically sealed, energy saving, low-noise, easy to service.
- Door frame heater prevents icing of the door.

Specification

	FROSTER LABO 530	FROSTER LABO 730
Capacity	500 litres	700 litres
Temperature setting	approx5 °C to -30 °C	approx5 °C to -30 °C
Voltage	220 – 240 V, 50 Hz	220 – 240 V, 50 Hz
Power consumption	605 watts	605 watts
Normal consumption	7.22 kWh/24 h	7.51 kWh/24 h
Admissible ambient temperature	from +10 °C to +32 °C	from +10 °C to +32 °C
Heat emission (max.)	753 watts	753 watts
Exterior dimensions (including door handle and distance from wall)	w x d x h = 77 x 76 x 193 - 196 cm	w x d x h = 77 x 98 x 193 - 196 cm
Interior dimensions	w x d x h =* 62 x 57 x 140 cm	w x d x h =* 62 x 77 x 140 cm
Exterior dimensions with door open at 90°	w x d = 77 x 144 cm	w x d = 77 x 165 cm
Shelf size	w x d = 59 x 45 cm	w x d = 59 x 65 cm
Max. load shelf	40 kg	40 kg
Weight	Net weight 140 kg, gross weight 183 kg	Net weight 165 kg, gross weight 200 kg

^{*}usable width 2 cm, usable depth 11 cm, usable height 13 cm less.

Optional equipment

- LED-Illumination mounted on side wall.
- Decorative door frame for attaching the customer's decorative plates.
- Adjustable feet to compensate for uneven floors. Watercooled refrigerating machine.
- Housing made of stainless steel 4301, longitudinal brushed.
- Plastic-drawer on roller runners (only FROSTER-LABO-530) w x d x h = $57 \times 39 \times 5.6 \text{ cm}$ (a maximum of twelve drawers is possible).
- Aluminium-drawer on roller runners FROSTER-LABO-530: $w \times d \times h = 56 \times 39 \times 10 \text{ cm}$, FROSTER-LABO-730: $w \times d \times h = 56 \times 60 \times 10 \text{ cm}$, (a maximum of eight drawers is possible).
- Additional length and cross dividers (for drawer).
- Stainless steel drawer (liquid tight) FROSTER-LABO-530: w x d x h = $56 \times 39 \times 10 \text{ cm}$, FROSTER-LABO-730: $w \times d \times h = 56 \times 60 \times 10 \text{ cm}$, (a maximum of eight drawers is possible).
- Additional shelf on rails or overlays.
- Basket on rails FROSTER-LABO-530: w x d x h = $60 \times 45 \times 10 \text{ cm}$, FROSTER-LABO-730: $w \times d \times h = 60 \times 65 \times 10 \text{ cm}$.
- Aluminium tray with rails FROSTER-LABO-530: w x d x h = $60 \times 40 \times 2.5 \text{ cm}$, FROSTER-LABO-730: w x d x h = $60 \times 65 \times 2.5 \text{ cm}$.
- **GSM-Module** for alarm text message transmission.
- Temperature documentation.